



Kinetis® K28-150 MHz, 2x USB, Core Voltage Bypass, 2MB Flash, 1MB SRAM MCUs based on Arm® Cortex®-M4

K28_150

Last Updated: Jan 16, 2023

The Kinetis K28 USB Arm® Cortex®-M4 MCUs target applications requiring processing efficiency and extra-large embedded memory with 2 MB Flash and 1 MB SRAM. This microcontroller sub-family is:

- Highly integrated with two I2S interfaces, two USB Controllers (High-Speed with integrated High-Speed PHY and Full-Speed) and mainstream analog peripherals
- Expandable through a 32-bit SDRAM memory controller and QuadSPI interface supporting eXecution-In-Place (XiP)
- Enabling secure content using a True Random Number Generator, Cyclic Redundancy Check, Memory Mapped Cryptographic Acceleration Unit


3 Input supply voltage rails: (1.2V, 1.8V and 3V) + separate VBAT domain

K28 implements a Power Management Controller supporting Core Voltage Bypass and can be powered by an external PMIC to maximize the power efficiency of the overall system

Packages: 169 MAPBGA (9x9mm², 0.65mm pitch) and 210 WLCSP (6.9x6.9mm², 0.4 mm pitch)

Evaluation / Development platform: FRDM-K28F

Kinetis K27/K28 USB MCUs Block Diagram Block Diagram



View additional information for [Kinetis® K28-150 MHz, 2x USB, Core Voltage Bypass, 2MB Flash, 1MB SRAM MCUs based on Arm® Cortex®-M4](#).

Note: The information on this document is subject to change without notice.

www.nxp.com

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2024 NXP B.V.