

| | |
|------------------------------|---|
| | <ul style="list-style-type: none"> • MC56F83xxx: Performance Level Digital Signal Controllers, USB FS OTG, CAN FD • S32K1: S32K1 車載向け汎用マイクロコントローラ |
| Power stage driver | <ul style="list-style-type: none"> • MC33937: 3-Phase Field Effect Transistor Pre-Driver • GD3100: Advanced High Voltage Isolated Gate Driver for IGBT and SiC MOSFETs |
| Motor Control Software | <ul style="list-style-type: none"> • FreeMASTERランタイム・デバッグ・ツール • RTCESL: Real Time Control Embedded Software Motor Control and Power Conversion Libraries • モデルベース設計ツールボックス (MBDT) • Motor Control Application Tuning (MCAT) Tool |
| Voltage regulator | <ul style="list-style-type: none"> • PCA9410_9410A: 3.0 MHz, 500 MA, DC-to-DC Boost Converter • MC33903: SBC Gen2 with High-Speed CAN and LIN • MC33904: System Basis Chip Gen2 with High Speed CAN • MC33905: SBC Gen2 with High-Speed CAN and LIN |
| Security (EdgeLock Discrete) | <ul style="list-style-type: none"> • SE050: EdgeLock[®] SE050 : Plug & Trustセキュア・エレメント・ファミリー - 柔軟性に優れた、IoT向けの高度なセキュリティ |
| Security (EdgeLock Discrete) | <ul style="list-style-type: none"> • SE050: EdgeLock[®] SE050 : Plug & Trustセキュア・エレメント・ファミリー - 柔軟性に優れた、IoT向けの高度なセキュリティ |

View our complete solution for [永久磁石同期モータ \(PMSM\)](#).

Note: The information on this document is subject to change without notice.

www.nxp.com

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2024 NXP B.V.