



© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.	MECHANICAL OUTLINE	PRINT VERSION NOT TO SCALE
TITLE: NI-880XS-2L4S	DOCUMENT NO: 98ASA00477D REV: A	
	STANDARD: NON-JEDEC	
	19 APR 2013	



NOTES:

1. CONTROLLING DIMENSION: INCH.

2. INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M-1994.

3. DIMENSIONS H1 AND H2 ARE MEASURED .030 INCH (0.762 MM) AWAY FROM FLANGE PARALLEL TO DATUM B. H1 APPLIES TO PINS 2 & 5. H2 APPLIES TO PINS 1, 3, 4 & 6.

4. TOLERANCE OF DIMENSION H2 IS TENTATIVE.

DIM	INCH		MILLIMETER		DIM	INCH		MILLIMETER	
	MIN	MAX	MIN	MAX		MIN	MAX	MIN	MAX
AA	.905	.915	22.99	23.24	R	.365	.375	9.27	9.53
BB	.380	.390	9.65	9.91	S	.365	.375	9.27	9.53
CC	.125	.170	3.18	4.32	U	.035	.045	0.89	1.14
D	.595	.605	15.11	15.37	V1	.895	.905	22.73	22.99
E	.035	.045	0.89	1.14	W1	.165	.175	4.19	4.45
F	.004	.007	0.10	0.18	W2	.315	.325	8.00	8.26
H1	.057	.067	1.45	1.70	W3	.425	.435	10.80	11.05
H2	.054	.070	1.37	1.78	Y	1.056 BSC		26.82 BSC	
K	.170	.210	4.32	5.33	Z	R.000	R.040	R.00	R1.02
K1	.070	.090	1.78	2.29	aaa	.005		0.13	
M	.874	.886	22.20	22.50	bbb	.010		0.25	
N	.872	.888	22.15	22.56	ccc	.015		0.38	

© FREESCALE SEMICONDUCTOR, INC.
ALL RIGHTS RESERVED.

MECHANICAL OUTLINE

PRINT VERSION NOT TO SCALE

TITLE:

NI-880XS-2L4S

DOCUMENT NO: 98ASA00477D

REV: A

STANDARD: NON-JEDEC

19 APR 2013